

# Altronix T1HCK3F4 Access and Power Integration Installation Guide

Home » Altronix » Altronix T1HCK3F4 Access and Power Integration Installation Guide





# T1HCK3F4 Access and Power Integration Installation Guide

#### **Contents**

- 1 Access & Power Integration
- 2 Installation Guide
- 3 Overview:
- **4 Configuration Chart:**
- **5 Hardware and Accessories:**
- **6 Installation Instructions:**
- **7 T1HCK3F: Configuration of Hartmann Controls Boards:**
- 8 T1HCK3F4: Configuration of Hartmann Controls

## **Boards:**

- 9 Features:
- 10 LINQ2 Mounts Inside any Trove Enclosure
- 11 Documents / Resources
  - 11.1 References
- 12 Related Posts

# **Access & Power Integration**

T1HCK3F Up to 8 Door Kit Fully assembled kit includes:

• Trove1 enclosure with THC1 Altronix/Hartmann Controls backplane

• One (1) eFlow6NB - Power Supply/Charger

#### T1HCK3F4

Up 8 Door Kit with Fused Outputs Fully assembled kit includes:

- Trove1 enclosure with THC1 Altronix/Hartmann Controls backplane
- One (1) eFlow6NB Power Supply/Charger
- One (1) ACM4 Fused Access Power Controller

All components of these Trove kits are UL Listed as sub-assemblies.

Please refer to the included corresponding Sub-Assembly Installation Guides for further information.

#### **Installation Guide**

All registered trademarks are the property of their respective owners.

Installing Company:	Service Rep. Name:	
Address:		Phone #:

#### Overview:

Altronix/Hartmann Controls Trove kits are pre-assembled and consist of a Trove enclosure with factory-installed Altronix power supply/chargers and sub-assemblies. Each kit also accommodates one (1) Hartmann Controls PRS\_Master board and up to four (4) PRS\_TDM or PRS\_IO8 boards.

# **Configuration Chart:**

Altronix Model Nu mber	120 VA C 6 0Hz Inp ut Cur rent (A)	ew er Sup ply Boa rd put Fus e R atin g		Nominal DC Output Voltage Options			Maximum		put (A)	;M4		
				[DC] [AUX]		[AUX]	Supply Current for		Fail-	(71)	Boa rd	AC M4
			Po wer Sup ply Bc Batt ery Fus e R at	12VD C Output Range (V)	24VD C Output Range (V)	12VD C Output Range 01)	24VD C Output Range (V)	Main and Aux. Outputs o n Power Supply board a nd ACM4 Access Power Controller's outputs (A)	Safe/F ail-Sec ure or Dry Fo rm "C" Output s		put Fus e R atin g	Boa rd Out put Fus e R atin g
T1HCK3F	4.	5A/ 250 V	15A / 32V	Flow6NB e		12 or 24VDC						
				10.0- 13.2	20.19- 26.4	10.03- 13.2	20.19- 26.4	@ 6A			_	_
T1HCK3F 4	4.	5A/ 250 V	15N 32V	eFlow6NB		12VDC @ 5.4			10A			
				10.0- 13.2	20.19- 26.4	10.03- 13.2	20.19- 26.4	A or 24VDC @ 5.7 A	4	3.	/ 32V	3N 32V

## **Hardware and Accessories:**




# **Installation Instructions:**

Wiring methods shall be in accordance with the National Electrical Code/NFPA 70/ANSI, and with all local codes and authorities having jurisdiction.

The product is intended for indoor use only.

- 1. Remove backplane from the enclosure. Do not discard hardware.
- 2. Mark and predrill holes in the wall to line up with the top three keyholes in the enclosure. Install three upper fasteners and screws in the wall with the screw heads protruding. Place the enclosure's upper keyholes over the three upper screws; level and secure.
  - Mark the position of the lower three holes. Remove the enclosure. Drill the lower holes and install the three fasteners. Place the enclosure's upper keyholes over the three upper screws.
- Install the three lower screws and make sure to tighten all screws.
- 3. Mount included UL Listed tamper switch (Altronix Model TS112 or equivalent) in the desired location, opposite hinge. Slide the tamper switch bracket onto the edge of the enclosure approximately 2" from the right side (Fig. 1, pg. 2). Connect the tamper switch wiring to the Access Control Panel input or the appropriate UL Listed reporting device. To activate the alarm signal open the door of the enclosure.
- 4. Mount Hartmann Controls boards to the backplane, refer to pages 3-4.
- 5. Refer to the eFlow Power Supply/Charger Installation Guide for eFlow6NB and



# T1HCK3F: Configuration of Hartmann Controls Boards:


- 1. Align the Hartmann Controls boards on the backplane to match the boards' mounting holes with the corresponding poems.
- 2. Fasten spacers (provided) to poems that match the hole pattern for Hartmann Control boards (Fig. 2, 2a, pg. 3).


Note: Hartmann Controls boards must be properly grounded.

Please use provided metal spacers for the lower right mounting holes (Fig. 2, pg. 3).

- 3. Mount Hartmann Controls boards to spacers utilizing provided 5/16" pan head screws (Fig. 2a, pg. 3).
- 4. Fasten backplane to Trove1 enclosure utilizing lock nuts (provided).

Fig. 2 – T1HCK3F Configurations





# T1HCK3F4: Configuration of Hartmann Controls Boards:


- 1. Align the Hartmann Controls boards on the backplane to match the boards' mounting holes with the corresponding poems.
- 2. Fasten spacers (provided) to poems that match the hole pattern for Hartmann Control boards (Fig. 3, 3a, pg. 4).


Note: Hartmann Controls boards must be properly grounded.

Please use provided metal spacers for the lower right mounting holes (Fig. 3, pg. 4).

- 3. Mount Hartmann Controls boards to spacers utilizing provided 5/16" pan head screws (Fig. 3a, pg. 4).
- 4. Fasten backplane to Trove1 enclosure utilizing lock nuts (provided).


# Fig. 3 – T1HCK3F4 Configurations





#### Notes:

eFlow Power Supply/Chargers can be Controlled and Monitored while Reporting Power/Diagnostics from Anywhere over the Network...




LINQ2 provides remote IP access to real-time data from eFlow power supply/chargers to help keep systems up and running at optimal levels. It facilitates fast and easy installation and set-up, minimizes system downtime, and eliminates unnecessary service calls, which helps reduce the Total Cost of Ownership (TCO) – as well as creates a new source of Recurring Monthly Revenue (RMR).


#### Features:

- UL is Listed in the U.S. and Canada.
- Local or remote control of up to (2) two Altronix eFlow power output(s) via LAN and/or WAN.
- Monitor real-time diagnostics: DC output voltage, output current, AC & battery status/service, input trigger state change, output state change and unit temperature.
- Access control and user management: Restrict read/write, Restrict users to specific resources
- Two (2) integral network controlled Form "C" Relays.
- Three (3) programmable input triggers: Control relays and power supplies via external hardware sources.
- · Email and Windows Dashboard notifications
- · The event log tracks history.
- Secure Socket Layer (SSL).
- Programmable via USB or web browser includes operating software and 6 ft. USB cable.

# **LINQ2 Mounts Inside any Trove Enclosure**



**Enclosure Dimensions** (H x W x D approximate): 18" x 14.5" x 4.625" (457mm x 368mm x 118mm)



Hartmann Controls is not responsible for any typographical errors.

10 Lockhart Rd, Barrie, ON L4N 9G8, Canada | phone: 1-877-411-0101
web site: <a href="mailto:www.hartmann-controls.com">www.hartmann-controls.com</a> | e-mail: <a href="mailto:sales@hartmann-controls.com">sales@hartmann-controls.com</a> | Made in the U.S.A.

IITHC1 Kit Series F11U

## **Documents / Resources**



# References

- Motion Control Control Solutions LLC
- **(P)** Hartmann

Manuals+,