

Wiha 76000

Wiha 76000 SoftFinish CentroFix Bit Holder User Manual

Model: 76000 | Brand: Wiha

1. INTRODUCTION

The Wiha 76000 SoftFinish CentroFix Bit Holder is a precision tool designed for securely holding various screwdriver bits. Manufactured in Germany, it features an ergonomic cushion grip handle and a unique CentroFix quick-release mechanism with four locking ball bearings to minimize bit wobble and ensure a firm hold. This manual provides instructions for its proper use, maintenance, and specifications.

Key Features:

- **Ergonomic Cushion Grip Handle:** Designed for comfort and enhanced control during prolonged use.
- **CentroFix Quick Release Bit Holder:** Features a magnetic mechanism that securely holds power bits and 90mm blades.
- **Dual Durometer Construction:** Ensures long-lasting durability and resilience.
- **Permanent Bond:** The handle is directly molded to the blade holder, creating a strong, permanent connection.
- **Parallel Flats:** Integrated design feature to prevent the tool from rolling off surfaces.

2. SETUP AND BIT INSERTION

The CentroFix bit holder is designed for quick and secure bit changes. Follow these steps to insert and remove screwdriver bits.

2.1 Inserting a Bit:

1. Hold the bit holder firmly in one hand.
2. Grasp the knurled collar of the bit holder with your other hand.
3. Pull the collar forward (away from the handle) to open the locking mechanism.
4. Insert the desired 1/4" hex screwdriver bit into the opening until it seats fully.

5. Release the collar. The four internal locking ball bearings will engage, securing the bit firmly in place.



Image: The Wiha 76000 SoftFinish CentroFix Bit Holder with a standard 1/4" hex bit securely inserted, demonstrating the ready-to-use configuration.



Image: A close-up view of the CentroFix quick-release mechanism, showing the knurled collar and the bit insertion point. Arrows

indicate the direction to pull the collar for bit release.

2.2 Removing a Bit:

1. Hold the bit holder firmly.
2. Pull the knurled collar forward (away from the handle) to disengage the locking mechanism.
3. While holding the collar forward, pull the bit straight out.
4. Release the collar once the bit is removed.

3. OPERATING INSTRUCTIONS

The Wiha 76000 SoftFinish CentroFix Bit Holder is designed for manual fastening tasks. Its robust design and secure bit retention make it suitable for a wide range of applications.

3.1 General Use:

- Select the appropriate 1/4" hex bit for your fastener.
- Insert the bit as described in Section 2.1.
- Position the bit onto the fastener head.
- Apply firm, steady pressure to the handle while rotating to tighten or loosen the fastener. The ergonomic handle provides excellent grip and torque transfer.
- The CentroFix mechanism ensures minimal bit play, enhancing control and reducing cam-out.



Image: The Wiha 76000 SoftFinish CentroFix Bit Holder, showcasing its ergonomic handle and bit holder mechanism from a top-down view.



Image: An angled view of the Wiha 76000 SoftFinish CentroFix Bit Holder, highlighting the handle's contour and the bit holder's design.



Image: A side profile of the Wiha 76000 SoftFinish CentroFix Bit Holder, showing the "Made in Germany" inscription on the handle.

3.2 Compatibility:

The CentroFix bit holder is compatible with standard 1/4" hex bits (C6 and E6 style), including power bits and 90mm blades. Its design minimizes play even with bits not specifically designed for it, such as certain Japanese bits with 13mm anvils.



Image: The Wiha 76000 SoftFinish CentroFix Bit Holder displayed alongside various types of screwdriver bits, illustrating its broad compatibility.

3.3 Product Demonstration Video:

Your browser does not support the video tag.

Video: A demonstration of the Wiha CentroFix bit holder, showcasing its secure bit retention with various bit types and minimal wobble. This video highlights the product's key functionality and German engineering.

4. MAINTENANCE

Proper maintenance ensures the longevity and optimal performance of your Wiha 76000 SoftFinish CentroFix Bit Holder.

- **Cleaning:** Wipe the handle and bit holder mechanism with a clean, dry cloth after each use to remove dirt, dust, and debris. For stubborn grime, a slightly damp cloth with mild soap can be used, followed by thorough drying.
- **Lubrication:** Periodically, apply a small amount of light machine oil to the moving parts of the quick-release mechanism to ensure smooth operation. Avoid over-lubrication.
- **Storage:** Store the bit holder in a dry environment, away from excessive moisture or corrosive chemicals, to prevent rust and material degradation.

- **Inspection:** Regularly inspect the bit holder for any signs of wear, damage, or loose components. Discontinue use if significant damage is observed.

5. TROUBLESHOOTING

This section addresses common issues you might encounter with your bit holder.

Problem	Possible Cause	Solution
Bit does not lock securely.	Debris in mechanism; worn bits; collar not fully released.	Clean the mechanism. Ensure bits are standard 1/4" hex and in good condition. Confirm collar snaps back into place after bit insertion.
Bit is difficult to remove.	Mechanism is dirty or dry; bit is stuck due to torque.	Clean and lightly lubricate the mechanism. Ensure the collar is pulled fully forward before attempting to remove the bit.
Excessive bit wobble.	Non-standard bit size; worn bit; internal mechanism issue.	Ensure you are using standard 1/4" hex bits. Replace worn bits. If the issue persists with new, standard bits, contact Wiha customer support.

6. SPECIFICATIONS

Attribute	Detail
Brand	Wiha
Model Name	76000
Part Number	76000
Head Style	Power Blade Holder (CentroFix Quick Release)
Material	Blend (Dual Durometer Handle)
Color	Multi (Red/Black)
Size	One Size
Item Weight	3.84 ounces
Product Dimensions (L x W x H)	1 x 1 x 1 inches (Approximate, as per data)
Recommended Uses	Home Improvement, Auto Repair
Special Feature	Soft Grip, CentroFix Quick Release
Included Components	SoftFinish Cushion Grip Blade Holding Screwdriver (Bit Holder)
Batteries Required?	No
UPC	084705760001

7. WARRANTY AND SUPPORT

Wiha products are manufactured to high-quality standards. For information regarding product warranty, returns, or technical support, please refer to the official Wiha website or contact their customer service department. Keep your purchase receipt as proof of purchase.

For additional resources and product information, visit the [Wiha Store on Amazon](#).