

Manuals.plus /

> [TRIXIE](#) /

> Trixie 39314 Interior Padding for Aluminum Transport Box Model 39344 (L-XL) User Manual

TRIXIE 39314

Trixie 39314 Interior Padding for Aluminum Transport Box Model 39344 (L-XL) User Manual

Brand: **TRIXIE** | Model: **39314**

1. INTRODUCTION AND OVERVIEW

This manual provides detailed instructions for the Trixie 39314 Interior Padding, specifically designed for use with the Trixie Aluminum Transport Box Model 39344 (L-XL size). This padding is engineered to enhance the comfort and safety of your pet during transport, offering insulation and stable support.

2. PRODUCT FEATURES

The Trixie 39314 Interior Padding incorporates several key features to ensure optimal pet comfort and product durability:

- Constructed from durable **polyester** material.
- Provides an **insulating effect** to maintain a comfortable temperature for your pet.
- Features **dimensionally stable foam** that retains its shape over time.
- Offers effective **padding during driving**, reducing impact and vibrations.
- Equipped with a **removable cover** for easy cleaning and maintenance.

3. SETUP AND INSTALLATION

The Trixie 39314 Interior Padding is designed for straightforward installation into the compatible Trixie Aluminum Transport Box Model 39344 (L-XL).

Installation Steps:

1. **Unpack the Padding:** Carefully remove the interior padding from its packaging.
2. **Prepare the Transport Box:** Ensure your Trixie Aluminum Transport Box Model 39344 (L-XL) is clean and free of debris.
3. **Position the Base:** Place the base section of the padding onto the floor of the transport box.

4. **Install Side Panels:** Position the side panels of the padding against the interior walls of the transport box. The padding is designed to fit snugly.
5. **Adjust for Fit:** Gently press and adjust the padding to ensure it sits flush against all interior surfaces, providing maximum coverage and stability.



An image showing the Trixie 39314 Interior Padding, a light grey, two-part cushion designed to fit inside an aluminum transport box, providing comfort and insulation.

4. OPERATING AND USAGE

Once correctly installed, the Trixie Interior Padding provides a comfortable and secure environment for your pet during travel. It is designed for continuous use within the transport box.

Benefits During Transport:

- **Enhanced Comfort:** The soft, stable foam provides a cushioned surface for your pet to rest on, reducing discomfort during long journeys.
- **Temperature Regulation:** The insulating properties help to maintain a more consistent temperature inside the transport box, protecting your pet from extreme heat or cold.
- **Reduced Stress:** A comfortable and secure environment can help reduce stress and anxiety for pets during travel.
- **Protection:** The padding acts as a barrier, protecting your pet from direct contact with the hard surfaces of the aluminum box and absorbing minor impacts.

5. MAINTENANCE

Regular cleaning and maintenance will ensure the longevity and hygiene of your Trixie Interior Padding, providing a fresh environment for your pet.

Cleaning Instructions:

- 1. Remove the Cover:** Unzip or unfasten the removable cover from the foam padding.
- 2. Washing:** The polyester cover can typically be machine washed on a gentle cycle with mild detergent. Refer to any specific care labels on the product for precise washing temperatures.
- 3. Drying:** Air dry the cover completely. Avoid high heat drying, which may damage the fabric.
- 4. Foam Care:** The foam insert itself can be spot cleaned with a damp cloth and mild soap if necessary. Ensure it is completely dry before reassembling.
- 5. Reassemble:** Once both the cover and foam are dry, carefully place the foam back into the cover and secure it. Reinstall the padding into the transport box.

6. TROUBLESHOOTING

This section addresses common questions and minor issues you might encounter with your Trixie Interior Padding.

Common Issues and Solutions:

- Padding does not fit correctly:**
Solution: Ensure you have the correct size padding (L-XL) for your Trixie Aluminum Transport Box Model 39344. Re-adjust the panels to ensure they are flush against the box walls.
- Difficulty removing or re-attaching the cover:**
Solution: Ensure all zippers or fasteners are fully opened. When re-attaching, align the foam carefully within the cover before zipping or fastening. Do not force the cover.
- Padding appears flattened or deformed:**
Solution: The foam is designed to be dimensionally stable. If flattening occurs, ensure it is not being stored under heavy objects. Allow it to air out and regain its shape. If deformation persists, contact customer support.

7. SPECIFICATIONS

Key technical specifications for the Trixie 39314 Interior Padding:

Specification	Detail
Model Number	39314
Compatible Transport Box Model	Trixie Aluminum Transport Box #39344
Size	L-XL
Material	Polyester
Color	Grey
Product Dimensions (L x W x H)	75 x 78 x 12 cm (approximate, for padding itself)
Weight	230 grams

8. WARRANTY AND SUPPORT

For specific warranty information regarding your Trixie 39314 Interior Padding, please refer to the documentation provided at the time of purchase or visit the official TRIXIE website. For further assistance, product inquiries, or to report any issues, please contact TRIXIE customer support directly.

© 2023 TRIXIE. All rights reserved. This manual is for informational purposes only.

ASK A QUESTION ABOUT THIS MANUAL

Ask about setup, troubleshooting, compatibility, parts, safety, or missing instructions. Manuals+ will review the question and use this page's manual context to help answer it.

Name

Anonymous

Email

you@example.com

After a successful submission, we securely hash the supplied account or form email before sending it to Microsoft Advertising for conversion attribution. [Privacy details](#).

Question

Example: How do I reset this device or fix this error?

Details

Model number, symptoms, what you tried, or the section of the manual you are using.

Submit question

Open the live page

<https://manuals.plus/asin/B07XL466T8>

More documents and user manuals: <https://manuals.plus/>