

[Manuals.plus](#) /

› [Cornat](#) /

› Cornat KSDSC360 Geneva Light LED Toilet Seat User Manual

Cornat KSDSC360

Cornat KSDSC360 Geneva Light LED Toilet Seat User Manual

Brand: Cornat | **Model:** KSDSC360

1. PRODUCT OVERVIEW

The Cornat KSDSC360 Geneva Light LED Toilet Seat offers enhanced comfort and functionality for your bathroom. Featuring a high-quality MDF core for a warm seating experience, this toilet seat is equipped with an integrated LED night light that activates automatically via an acoustic sensor in the dark. Its Soft-Close mechanism ensures gentle and silent closing, while the Quick up & Clean function allows for easy removal and thorough cleaning. Designed for convenient top mounting, it is compatible with most standard wall-mounted and floor-standing toilets.



Image 1.1: Front view of the Cornat KSDSC360 Geneva Light LED Toilet Seat, showcasing its unique starry night and mountain design.

2. KEY FEATURES

- **Integrated LED Night Light:** Automatically illuminates in the dark for approximately 30 seconds upon detecting sound, providing a soft guide light.
- **Acoustic Sensor:** Activates the LED light based on sound detection in low-light conditions.

- **Soft-Close System:** Ensures the lid and seat close gently and silently, preventing slamming and reducing the risk of injury.
- **Quick up & Clean Function:** Allows for easy and quick removal of the entire seat for comprehensive cleaning without disassembling hinges.
- **High-Quality MDF Core:** Provides a pleasant and warm seating sensation.
- **Durable and Hygienic Surface:** Smooth, water-repellent acrylic coating is easy to clean with standard cleaning products.
- **Top Mounting:** Designed for comfortable and convenient installation from above.
- **Universal Fit:** Suitable for mounting on most common wall-mounted and floor-standing toilets.
- **Maximum Load Capacity:** Supports up to 150 kg.

3. SETUP AND INSTALLATION

The Cornat KSDSC360 toilet seat is designed for straightforward top mounting. Please ensure you have 3 AAA batteries (not included) for the LED light function before installation.

3.1 Pre-Installation Check

- Verify that the toilet seat dimensions (outer: 43.5 x 37 cm, inner: 28.5 x 23.2 cm) are compatible with your toilet bowl. Refer to the dimension diagram below.
- Ensure all mounting accessories are present in the package.
- Insert 3 AAA batteries into the designated battery compartment for the LED light.



Produkt-Abmessungen




Image 3.1: Product dimensions diagram, indicating outer and inner measurements, hinge spacing, and maximum load capacity.

3.2 Mounting Procedure

1. Position the mounting hinges over the toilet bowl holes.
2. Insert the provided screws and fasteners through the hinges and into the toilet bowl holes from the top.
3. Tighten the fasteners securely to ensure the hinges are firmly attached.
4. Align the toilet seat with the installed hinges and press down until it clicks into place. The Quick up & Clean mechanism allows for easy attachment and detachment.



Image 3.2: Detail of the top-mounting hinges, illustrating the secure attachment points.

4. OPERATING INSTRUCTIONS

4.1 LED Night Light

- The integrated LED light is designed to activate automatically in dark environments.
- When an acoustic sensor detects sound (e.g., footsteps, a door opening) in a dimly lit room, the LED light will turn on for approximately 30 seconds.
- Ensure fresh AAA batteries are installed for optimal performance.



Image 4.1: The toilet seat's LED light providing soft illumination in a dark bathroom setting.

4.2 Soft-Close Function

- To engage the Soft-Close function, simply push the lid or seat down gently.
- The integrated mechanism will take over, allowing the lid and seat to lower slowly and quietly until fully closed.

5. MAINTENANCE AND CLEANING

Regular cleaning will maintain the hygiene and appearance of your toilet seat.

5.1 Quick up & Clean Removal

1. To remove the toilet seat for thorough cleaning, locate the release buttons or levers on the hinges.
2. Press or lift these mechanisms to detach the seat from the mounting posts.
3. Once detached, the seat can be easily lifted off for cleaning.





Image 5.1: The toilet seat lifted, demonstrating the Quick up & Clean function for easy access to all surfaces.

5.2 Cleaning Instructions

- Use mild soap and water or standard bathroom cleaning products.
- Wipe the surfaces with a soft cloth or sponge.
- Avoid abrasive cleaners, harsh chemicals, or scouring pads, as these can damage the acrylic coating.
- Ensure the battery compartment remains dry during cleaning.

- After cleaning, reattach the seat by aligning it with the hinges and pressing down until it locks securely.

6. TROUBLESHOOTING

If you encounter any issues with your Cornat KSDSC360 toilet seat, please refer to the following common solutions:

- **LED Light Not Working:**
 - Check if 3 AAA batteries are correctly installed.
 - Replace old batteries with new ones.
 - Ensure the room is sufficiently dark for the acoustic sensor to activate.
- **Soft-Close Not Functioning Properly:**
 - Verify that the hinges are securely tightened and not loose.
 - Ensure no obstructions are preventing the smooth closing of the lid or seat.
 - Clean the hinge mechanisms to remove any dirt or debris.
- **Seat Feels Loose or Wobbly:**
 - Re-tighten the mounting screws from the top.
 - Ensure the seat is correctly engaged with the Quick up & Clean hinge posts.

7. SPECIFICATIONS

Feature	Detail
Model Number	KSDSC360
Design/Pattern	Geneva Light
Shape	Oval
Mounting Type	Top Mounting
Outer Dimensions (L x W)	43.5 cm x 37 cm
Inner Dimensions (L x W)	28.5 cm x 23.2 cm
Hinge Spacing	11 - 19 cm (adjustable)
Maximum Load Capacity	150 kg
Weight	3 kg
Seat Material	MDF (Engineered Wood)
Lid Surface Material	Acrylic
Hinge Material	Plastic/Metal
LED Power Source	3 x AAA Batteries (not included)

Feature	Detail
Country of Origin	China

8. WARRANTY AND SUPPORT

For information regarding product warranty, returns, or technical support, please contact your retailer or the manufacturer directly. Keep your proof of purchase for any warranty claims.

Manufacturer: Conmetall

© 2025 Cornat. All rights reserved.

ASK A QUESTION ABOUT THIS MANUAL

Ask about setup, troubleshooting, compatibility, parts, safety, or missing instructions. Manuals+ will review the question and use this page's manual context to help answer it.

Name

Anonymous

Email

you@example.com

After a successful submission, we securely hash the supplied account or form email before sending it to Microsoft Advertising for conversion attribution. [Privacy details](#).

Question

Example: How do I reset this device or fix this error?

Details

Model number, symptoms, what you tried, or the section of the manual you are using.

Submit question

Open the live page

<https://manuals.plus/asin/B0857XKZQC>

More documents and user manuals: <https://manuals.plus/>