

ergounion E6

Ergounion Single Monitor Arm Desk Mount User Manual

MODEL: E6

Brand: ergounion

1. INTRODUCTION

Thank you for choosing the Ergounion Single Monitor Arm Desk Mount. This manual provides detailed instructions for the safe and efficient installation, operation, and maintenance of your new monitor arm. Designed for ergonomic comfort and space-saving, this mount supports monitors up to 40 inches and 25 lbs, featuring full adjustability and versatile mounting options.

For additional support or video guides, please refer to the official user guide PDF linked in the support section.

2. KEY FEATURES

- **Effortless Setup:** Quick installation in 3 steps with clear instructions.
- **Easy to Adjust:** Flexible movement structure for instant and effortless adjustments of viewing heights.
- **Maximize Desk Space:** Retractable arms and built-in cable management system for an organized workspace.
- **Universal Monitor Stand:** Fits most 13-40 inch monitors with loading capacity from 7 to 25 pounds (3.2-11.3 kgs). VESA compatible with 100 x 100 mm and 75 x 75 mm.
- **Wide Desks Compatibility:** Supports both C-clamp and grommet mount. C-clamp fits desks between 0.4 inches (10mm) and 2.4 inches (60mm). Grommet fits desks less than 2.25 inches (57mm) thick.

3. SAFETY INFORMATION

- Ensure your desk can support the combined weight of the monitor arm and your monitor.
- Do not exceed the maximum weight capacity of 25 lbs (11.3 kg).
- Always follow installation instructions carefully to prevent injury or damage.
- Keep children and pets away during installation.
- Avoid pinching fingers or cables during adjustment.

4. SETUP GUIDE

4.1. Unpacking and Component Check

Carefully remove all components from the packaging. Verify that all parts are present and undamaged. Refer to the included parts list in your physical manual for a complete inventory.



Image: Overview of the Ergounion Single Monitor Arm Desk Mount and its main components.

4.2. Choosing Your Mounting Option (C-Clamp or Grommet)

The monitor arm supports two installation methods: C-Clamp for desk edges or Grommet for desks with a pre-drilled hole.

- **C-Clamp Mount:** Suitable for desks with a thickness between 0.4 inches (10mm) and 2.4 inches (60mm).
- **Grommet Mount:** Requires a desk hole with a diameter between 0.4 inches (10mm) and 2.4 inches (60mm). Fits desks less than 2.25 inches (57mm) thick.

Hidden Cable Management




Image: Illustration showing the C-Clamp mounting method on the left and the Grommet mounting method on the right.

Follow the specific instructions provided in the physical manual for your chosen mounting method. Ensure the mount is securely fastened to the desk before proceeding.



Image: Visual guide for the general installation process, showing the assembly of the base, arm, and monitor attachment.

CAUTION: When installing the fasteners, DO NOT over-tighten the screws. Otherwise, it may damage the equipment or screws.

4.3. Attaching Your Monitor

The monitor arm supports VESA mounting patterns of 75x75mm and 100x100mm. Align the VESA plate on the arm with the mounting holes on the back of your monitor. Secure the monitor using the provided screws. Ensure the monitor is firmly attached before releasing it.




Image: A monitor securely attached to the VESA plate of the monitor arm, demonstrating the connection point.

5. OPERATING YOUR MONITOR ARM

5.1. Adjusting Monitor Position

The Ergounion monitor arm offers a wide range of motion for optimal viewing comfort. You can easily rotate, swivel, and tilt your monitor to your desired position. The arm features an articulating spring for smooth adjustments.

- **Rotation:** Rotate your monitor 360 degrees for landscape or portrait orientation.
- **Swivel:** Swivel the arm at various pivot points up to 360 degrees to share your screen or adjust viewing

angles.

- **Tilt:** Tilt your monitor from +90 degrees to -25 degrees to reduce glare and optimize viewing.
- **Height Adjustment:** Adjust the monitor height along the pole and via the articulating arm for ergonomic alignment.




Image: Diagram illustrating the full range of motion of the monitor arm, including rotation, swivel, and tilt angles.



Image: A hand demonstrating the ease of one-touch adjustment for the monitor arm, highlighting its flexible movement.

5.2. Cable Management

Utilize the integrated cable management system to keep your workspace tidy and organized. Route monitor cables through the designated channels along the arm to prevent clutter and potential hazards.

One-Touch Adjustment

For efficient work and
comfortable games playing

Easier and more
convenient



Image: Close-up view of the monitor arm showing cables neatly routed through its hidden management channels.

6. MAINTENANCE

- Regularly check all screws and connections to ensure they are secure.
- Clean the monitor arm with a soft, damp cloth. Avoid abrasive cleaners.
- Periodically check the tension of the articulating spring to ensure your monitor remains stable at the desired height. Adjust as needed (refer to Troubleshooting section).

7. TROUBLESHOOTING

7.1. Monitor Does Not Stay at Desired Height

If your monitor does not stay up when raised or sinks when lowered, the articulating spring tension needs adjustment. Use the provided Allen key to adjust the tension screw located on the arm.

Articulating Spring Monitor Arm



Turn Counter Clockwise for
LIGHTER Monitors



Turn Clockwise for
HEAVIER Monitors




Image: Close-up of the monitor arm showing the tension adjustment screw. Turn clockwise for heavier monitors (to increase tension) and counter-clockwise for lighter monitors (to decrease tension).

- If the monitor **does not stay up** when raised, turn the tension screw **clockwise (+)** to increase tension until it stays at your desired height.

- If the monitor **does not stay down** when lowered, turn the tension screw **counter-clockwise (-)** to reduce tension until it stays at your desired height.

8. SPECIFICATIONS

Specification	Value
Brand	ergounion
Model Number	E6
Item Weight	7.48 pounds
Product Dimensions	16.7 x 10.2 x 5.7 inches
Color	Silver
Material	Aluminum
Mounting Type	Tabletop Mount (C-Clamp, Grommet)
Movement Type	Rotate, Swivel, Tilt
Maximum Compatible Size	40 Inches
Minimum Compatible Size	13 Inches
Weight Capacity	7 to 25 lbs (3.2-11.3 kgs)
VESA Compatibility	75 x 75 mm, 100 x 100 mm
Maximum Tilt Angle	90 Degrees
UPC	768432173067

9. WARRANTY & SUPPORT

For warranty information and customer support, please refer to the documentation included with your product or visit the official Ergounion website. You can also find a detailed installation manual in PDF format here: [Ergounion Installation Manual \(PDF\)](#).

Please note: No official seller videos were available for embedding based on the provided criteria. Refer to the PDF manual for visual instructions if needed.

© 2024 Ergounion. All rights reserved.

ASK A QUESTION ABOUT THIS MANUAL

Ask about setup, troubleshooting, compatibility, parts, safety, or missing instructions. Manuals+ will review the question and use this page's manual context to help answer it.

Name

Anonymous

Email

you@example.com

After a successful submission, we securely hash the supplied account or form email before sending it to Microsoft Advertising for conversion attribution. [Privacy details](#).

Question

Example: How do I reset this device or fix this error?

Details

Model number, symptoms, what you tried, or the section of the manual you are using.

Submit question