

[Manuals.plus](#) /

> [AIKE](#) /

> AIKE AK1062 15fl.oz Liquid Soap Dispenser Instruction Manual

AIKE AK1062

AIKE AK1062 15fl.oz Liquid Soap Dispenser Instruction Manual

Model: AK1062 | Brand: AIKE



1. PRODUCT OVERVIEW

The AIKE AK1062 Liquid Soap Dispenser is designed for convenient dispensing of liquid soaps. Its matte black, anti-fingerprint coating provides a clean aesthetic, suitable for various environments such as kitchens and bathrooms. This dispenser holds up to 15 fluid ounces of liquid.



Image 1: Front view of the AIKE AK1062 Liquid Soap Dispenser.

2. SETUP AND FILLING

1. **Prepare for Filling:** Gently lift the top section of the dispenser to access the reservoir.
 2. **Fill with Liquid:** Pour your desired liquid soap (dish soap, hand soap, lotion) into the reservoir. Ensure not to use foaming soap, as this dispenser is not designed for it. An internal max fill line is present to prevent overfilling. The dispenser has a 15 fl.oz (approximately 450 ml) capacity.
 3. **Secure the Top:** Carefully place the top section back onto the dispenser, ensuring it is securely seated.
-

Exactly Size

15-oz/450-ml capacity
internal max fill line



Image 2: Demonstrating the easy refilling process of the dispenser.

3. OPERATING INSTRUCTIONS

To dispense soap, simply press down on the pump head with minimal effort. The dispenser is designed for smooth and consistent output.

**Spot resist
stainless
finish**



Image 3: Dispensing soap onto a sponge for dishwashing.

Easy pumping with minimal effort



Image 4: Dispensing soap into a bowl for general use.

The clear window at the base allows for easy monitoring of the liquid level, so you know when a refill is needed.

4. MAINTENANCE AND CARE

- **Cleaning:** The stainless finish is designed to resist fingerprints and water spots, contributing to a cleaner appearance. For general cleaning, wipe the exterior with a soft, damp cloth. Avoid abrasive cleaners that may damage the finish.
- **Preventing Leakage:** To ensure longevity and prevent potential leakage, avoid collisions or dropping the dispenser during daily use.
- **Soap Compatibility:** Use only liquid soaps, hand soaps, or lotions. Do not use foaming soaps, as they are incompatible with this dispenser's mechanism.

5. TROUBLESHOOTING

If you experience any issues with your AIKE AK1062 dispenser, consider the following:

- **No Dispensing:** Ensure the pump head is securely attached and the reservoir contains sufficient liquid. If the liquid is too thick, it may need to be diluted slightly.
- **Leakage:** Check for any visible damage or improper assembly of the top section. Ensure the dispenser is placed on a stable, flat surface to prevent accidental tipping.
- **Clogging:** If the pump appears clogged, try flushing it with warm water. Ensure you are using appropriate liquid soaps and not foaming varieties.

6. SPECIFICATIONS

Feature	Detail
Model Number	AK1062
Brand	AIKE
Color	Anti-fingerprint Black Coating
Material	Stainless Steel
Liquid Volume	15 Fluid Ounces
Product Dimensions	3.9"L x 3"W x 7.7"H
Item Weight	7 ounces
Material Type Free	PVC Free
Manufacturer	Zhejiang AIKE Appliances Co., Ltd.



Image 5: Product dimensions for the AIKE AK1062 dispenser.

7. WARRANTY AND SUPPORT

The AIKE AK1062 Liquid Soap Dispenser comes with a **1-Year Warranty**. For detailed warranty information and customer support, please refer to the official AIKE Store Page on Amazon or contact the manufacturer directly.

For further assistance, please visit the [AIKE Store on Amazon](#).

