



CallToU P4 Series Wireless Calling System Instruction Manual

[Home](#) » [CALLTOU](#) » CallToU P4 Series Wireless Calling System Instruction Manual 

Contents

- [1 CallToU P4 Series Wireless Calling System](#)
- [2 Product Information](#)
- [3 Product Usage Instructions](#)
- [4 Documents / Resources](#)

CallToU

CallToU P4 Series Wireless Calling System



Product Information

The Wireless Calling system P4 Series consists of a Receiver Model: P4 and a Call Button Model: E-01A/E-01AB.

It is designed to deliver users' help signal to caregivers in order to provide quality long-term care services for the elderly and those in need. The P4 Receiver comes with an AC Adapter, a Lanyard, a Digital Display Screen, a Hook Slot, an Antenna, a Loudspeaker, a USB Interface for Modify Voice, a Speaker Jack (3.5mm), an AC Socket, and a Detachable Bracket for wall-mounted installation. It has a 1000 feet operating range in open areas and features a Red Light Indicator after pressing the silicone cover. The receiver has a waterproof grade of IP55. The Call Button is powered by a 23A 12V alkaline battery (included) and has a waterproof standard of IP55. It has a diameter of 2.4 inches and a thickness of 0.7 inches. The button operates on a frequency of 433MHz and has a temperature range of -30 to +70 degrees Celsius.

Product Usage Instructions

1. To set up the system, please follow these steps:

- Read the manual carefully.
- Contact service01@calltou.com directly for any issues or assistance.

2. **Receiver Operation:**

- Press the [FUN] key for 3 seconds to enter or exit setting status.
- Press the [SET] key to adjust the number.
- Press the [MOVE] key to adjust the number position.
- Press the [ENT] key to confirm the setting.

3. **Receiver Specifications:**

- **Voltage:** 12V
- **Current:** 1A
- **Capacity:** Multiple up to 1000pcs wireless call button
- **Number range:** 0001~9999, A001~F999
- **Working Temperature:** -20-80 degrees Celsius
- **Receiving Sensitivity:** -105dBm
- **Frequency:** 433MHz

4. **Call Button Operation:**

- Press the button to send a help signal to caregivers.

5. **Call Button Specifications:**

- **Button battery:** 23A 12V alkaline battery (included)
- **Button Waterproof Standard:** IP55
- **Button Size:** Diameter 2.4 inch, thickness 0.7 inch
- **Temperature:** -30 to +70 degrees Celsius
- **Frequency:** 433MHz

6. **System Expansion:**

- The system is extendable with more receivers and call buttons.
- Other models of CallToU receivers and buttons can also work with this system.
- Contact customer service for more information.

7. **Video Guides:**

- **Storage Mode (F-01):** Suitable for adding/pairing additional transmitters
- **Deletion Mode (F-02):** Delete the transmitters that have been paired



P4 Receiver



AC Adapter



Lanyard
(5/10 PCS)



Call Button (5/10 PCS)
(white/black)
Contained Battery



Double Sided
Adhesive Tape



Screwdriver







STEP 1



STEP 2



STEP 3



STEP 4



STEP 1



STEP 2



STEP 3




STEP 4





Documents / Resources

	<p>CallToU P4 Series Wireless Calling System [pdf] Instruction Manual P4 Receiver, E-01A-E-01AB Call Button, P4 Series Wireless Calling System, Wireless Calling System, Calling System</p>
---	---

Manuals+.