


CSI Controls Rapid Set System Installation Guide

Home » CSI Controls » CSI Controls Rapid Set System Installation Guide ™







Contents

- 1 INSTALLATION
- **INSTRUCTIONS**
- 2 DIAGRAM
- 3 Documents / Resources
 - 3.1 References
- **4 Related Posts**

INSTALLATION INSTRUCTIONS


Do not remove side wood stabilizers until anchored to concrete.



LIFTING EYE CAPACITY: 700lbs combined max




Place Rapid Set on concrete pad.






Anchor Rapid Set to the concrete pad Only use specified anchor bolts, 4 bolts required

• 0.5 DIAMETER WEDGE ANCHOR, ICC APPROVED, MINIMUM TENSION CAPACITY OF 3000 LBS




Remove side wood stabilizers



* Some models do not include the sunshield.

DIAGRAM



Documents / Resources



<u>CSI Controls Rapid Set System</u> [pdf] Installation Guide Rapid Set System, Rapid, Set System, System

References

- O Home Primex Controls
- 5 Home SJE Rhombus Control Products
- User Manual

Manuals+, Privacy Policy

This website is an independent publication and is neither affiliated with nor endorsed by any of the trademark owners. The "Bluetooth®" word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. The "Wi-Fi®" word mark and logos are registered trademarks owned by the Wi-Fi Alliance. Any use of these marks on this website does not imply any affiliation with or endorsement.