

DIVERSITECH QSMS1201 Mini Split Stand Owner's Manual

Contents

- [1 DIVERSITECH QSMS1201 Mini Split Stand](#)
- [2 Product Information](#)
- [3 Product Usage Instructions](#)
- [4 Documents / Resources](#)



DIVERSITECH QSMS1201 Mini Split Stand




Product Information

Item No.	Part Number	Description	Default Quantity
1	MS107	Mini Split 12in J-Bar	4
2	MS106	Mini Split Extension Bar	2
3	MS119	Mini Split Long Saddle Arm	2
4	MS105	Mini Split 6×6 Feet	4
5	QSR008	1/4-20×1/2in Zinc Hex Bolt	8
6	QSR015	1/4in Bonded Washers	8
7	QSR042	Mini Split Rubber Foot	8
8	HDKMS01	Hardware kit for QSMS1200/1201	1


Product Usage Instructions

To use the product, follow these steps:


1. Ensure that all assembly hardware provided is included in the package.
2. Identify the specific parts needed based on the item numbers and descriptions mentioned in the table above.
3. Assemble the Mini Split 12in J-Bar (MS107) using the provided quantity of 4.
4. Attach the Mini Split Extension Bar (MS106) to the J-Bar using the provided quantity of 2.
5. Connect the Mini Split Long Saddle Arm (MS119) to the Extension Bar using the provided quantity of 2.
6. Secure the Mini Split 6×6 Feet (MS105) to the Long Saddle Arm using the provided quantity of 4.
7. Use the 1/4-20×1/2in Zinc Hex Bolt (QSR008) and the 1/4in Bonded Washers (QSR015) to fasten all components securely.
8. Attach the Mini Split Rubber Foot (QSR042) to provide stability.
9. Make sure to follow the Third Angle Projection and/or Seismic Load instructions provided by the installer to tether and bolt the units to withstand wind and other forces.




SIDE VIEW RETRACTED



SIDE VIEW EXPANDED



END VIEW RETRACTED




END VIEW EXPANDED

(*) – WIDTH IS ADJUSTABLE IN 1" INCREMENTS

IMPORTANT NOTE: THE INSTALLER IS RESPONSIBLE FOR THETHERING AND BOLTING UNITS TO WITHSTAND WIND AND/OR SEISMIC LOADS.


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	MS107	Mini Split 12in J-Bar	4
2	MS106	Mini Split Extension Bar	2
3	MS119	Mini Split Long Saddle Arm	2
4	MS105	Mini Split 6×6 Feet	4
5	QSR008	1/4-20×1/2in Zinc Hex Bolt	8
6	QSR015	1/4in Bonded Washers	8
7	QSR042	Mini Split Rubber Foot	8
8	HDKMS01	Haedware kit for QSMS1200/1201	1



NOTE – ALL ASSEMBLY HARDWARE IS INCLUDED

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES [MILLIMETERS]

- TOLERANCES ARE: ANGLES $\pm 1.0^\circ$
- FRACTIONAL SIZES X/Y $\pm 1/64$
- INCHES [MILLIMETERS]
- .X = ± 0.1 [X = ± 2.5]
- .XX = ± 0.01 [.X = ± 1.3]
- .XXX = ± 0.005 [.XX = ± 0.13]




CONFIDENTIAL – PROPRIETARY – DO NOT COPY
THE INFORMATION SET FORTH IN THIS DOCUMENT AND RELATED INFORMATION IS THE CONFIDENTIAL
PROPERTY OF DIVERSITECH CORPORATION, AND IS NOT TO BE COPIED OR REPRODUCED OR
DISTRIBUTED IN ANY FORM WITHOUT PRIOR WRITTEN PERMISSION FROM DIVERSITECH
CORPORATION.
DO NOT SCALE DRAWING

MATERIAL:
DWG. NO.
MINI SPLIT STAND – 1201 MODEL NO. QSMS1201

WEIGHT
GMS.
REV.

SHEET
2 OF 2

Documents / Resources



[DIVERSITECH QSMS1201 Mini Split Stand](#) [pdf] Owner's Manual
QSMS1201 Mini Split Stand, QSMS1201, Mini Split Stand, Split Stand, Stand