



# formlabs White Resin V5 Owner’s Manual

[Home](#) » [formlabs](#) » **formlabs White Resin V5 Owner’s Manual** 

**formlabs White Resin V5 Owner's Manual**

# White Resin V5

## An optimally-balanced White Resin for versatile applications

White Resin V5 is an exceptionally bright white General Purpose Resin, offering an optimal balance of fast print speed, high accuracy, presentation-ready appearance, strong mechanical properties, and an easy, reliable workflow.

Create parts that are stiff and strong with a surface finish that rivals injection molding. White Resin V5 is a matte, bright white that captures fine features accurately.

White Resin V5 is a new material formulation that leverages the Form 4 ecosystem to print three times faster than the previous version.

### Form and fit prototyping

### Presentation-ready models with fine features and intricate details

### Anatomical models

### Jigs and fixtures

**V5****FLGPWH05**

Prepared 20/03/2024

Rev. 01 20/03/2024

To the best of our knowledge the information contained herein is accurate. However, Formlabs, Inc. makes no warranty, expressed or implied, regarding the accuracy of these results to be obtained from the use thereof.

Material Properties	METRIC <sup>1</sup>			IMPERIAL <sup>1</sup>			METHOD
	Green	Post-Cured for 5 min at ambient temperature <sup>2</sup>	Post-Cured for 15 min at 60 °C <sup>3</sup>	Green	Post-Cured for 5 min at ambient temperature <sup>2</sup>	Post-Cured for 15 min at 140 °F <sup>3</sup>	
Tensile Properties	METRIC <sup>1</sup>			IMPERIAL <sup>1</sup>			METHOD
Ultimate Tensile Strength	46 MPa	54 MPa	62 MPa	6672 psi	7832 psi	8992 psi	ASTM D638-14
Tensile Modulus	2200 MPa	2500 MPa	2675 MPa	319 ksi	363 ksi	388 ksi	ASTM D638-14
Elongation at Break	22%	15%	13%	22%	15%	13%	ASTM D638-14
Flexural Properties	METRIC <sup>1</sup>			IMPERIAL <sup>1</sup>			METHOD
Flexural Strength	82 MPa	91 MPa	103 MPa	11893 psi	13198 psi	14938 psi	ASTM D790-15
Flexural Modulus	2000 MPa	2450 MPa	2750 MPa	290 ksi	355 ksi	399 ksi	ASTM D790-15
Impact Properties	METRIC <sup>1</sup>			IMPERIAL <sup>1</sup>			METHOD
Notched Izod	36 J/m	34 J/m	32 J/m	0.673 ft-lb/in	0.636 ft-lb/in	0.598 ft-lb/in	ASTM D4812-11
Thermal Properties	METRIC <sup>1</sup>			IMPERIAL <sup>1</sup>			METHOD
Heat Deflection Temp. @ 1.8 MPa	47 °C	54 °C	59 °C	117 °F	129 °F	138 °F	ASTM D648-16
Heat Deflection Temp. @ 0.45 MPa	55 °C	62 °C	71 °C	131 °F	144 °F	160 °F	ASTM D648-16

## Contents

### 1 SOLVENT COMPATIBILITY

### 2 Documents / Resources

#### 2.1 References

## SOLVENT COMPATIBILITY

Percent weight gain over 24 hours for a printed 1 x 1 x 1 cm cube immersed in respective solvent:

Solvent	24 hr weight gain, %	Solvent	24 hr weight gain, %
Acetic Acid 5%	0.9	Mineral oil (Heavy)	0.2
Acetone	4.9	Mineral oil (Light)	0.2
Bleach ~5% NaOCl	0.7	Salt Water (3.5% NaCl)	0.8
Butyl Acetate	0.3	Skydrol 5	0.5
Diesel Fuel	0.1	Sodium Hydroxide solution (0.025% PH 10)	0.8
Diethyl glycol Monomethyl Ether	1.0	Strong Acid (HCl conc)	0.5
Hydraulic Oil	0.2	Tripropylene glycol monomethyl ether	0.3
Hydrogen peroxide (3%)	0.9	Water	0.8
Isooctane (aka gasoline)	< 0.1	Xylene	< 0.1
Isopropyl Alcohol	0.3		

1. Material properties may vary based on part geometry, print orientation, print settings, temperature, and disinfection or sterilization methods used.
2. Data was obtained from parts printed on a Form 4 printer with 100 µm White Resin V5 settings, washed in a Form Wash for 5 minutes in 99% Isopropyl Alcohol, and post-cured at room temperature for 5 minutes in a Form Cure.
3. Data was obtained from parts printed on a Form 4 printer with 100 µm White Resin V5 settings, washed in a Form Wash for 5 minutes in 99% Isopropyl Alcohol, and post-cured at 60°C for 15 minutes in a Form Cure.

## Documents / Resources



[formlabs White Resin V5](#) [pdf] Owner's Manual  
V5 FLGPWH05, White Resin V5, Resin V5, V5, Resin

## References

- [User Manual](#)

### [Manuals+](#), [Privacy Policy](#)

This website is an independent publication and is neither affiliated with nor endorsed by any of the trademark owners. The "Bluetooth®" word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. The "Wi-Fi®" word mark and logos are registered trademarks owned by the Wi-Fi Alliance. Any use of these marks on this website does not imply any affiliation with or endorsement.