

# LEVITON MDS3-AC Power Switch Safety Disconnect Switch with Factory Installed Auxiliary Contact Instructions

Home » Leviton » LEVITON MDS3-AC Power Switch Safety Disconnect Switch with Factory Installed Auxiliary Contact Instructions

### **Contents**

- 1 LEVITON MDS3-AC Power Switch Safety Disconnect Switch with Factory Installed Auxiliary
- **2 Technical Information**
- 3 Documents / Resources
  - 3.1 References
- **4 Related Posts**



LEVITON MDS3-AC Power Switch Safety Disconnect Switch with Factory Installed Auxiliary



• Powerswitch® Safety Disconnect Switch with Factory Installed Auxiliary Contact

- 30 Amp, 600 Volt, Non-Fused Powerswitch Safety Disconnect Switch in Stainless Steel Enclosure with Factory Installed Auxiliary Contact
- Powerswitch® safety disconnect switches are designed for superior performance in food and beverage processing, manufacturing, marinas and shipyards, and OEM applications.
  - Type 304 stainless steel resists heat, corrosion, and abuse
  - · Watertight, dust-tight, submersible and suitable for high pressure, high temperature washdown
  - NSF Certified for hygiene requirements in food & beverage processing

#### **Technical Information**

# • Electrical Specifications

• Amperage: 30/32 A

Current Interrupting: Certified for full-rated current and voltage
Dielectric Voltage: 1000 V plus twice rated voltage for 1 minute

Endurance: 6,000 cycles inductive motor type load

• Short Circuit Current Rating: 10KA

• Voltage: 600 VAC

## Environmental Specifications

Ingress Protection: NEMA/UL 50E Type 3R, 4X, 12, 13; IP66, IP67, IP68; IP69K (per ISO 20653)

Operating Temperature : -40°C to 75°C

• UV Resistance : Exposed materials are UV stabilized

## Material Specifications

Enclosure Material: 16 Gauge Type 304 Stainless Steel

Gasket: Polyurethane Formed-In-Place-Foam Gasket (FIPFG), UL 50E Approved

## • Patents\*

US9828789

### · Handle Material

• Base: PBT

Overmold: TPE

## Mechanical Specifications

• Product ID: Part of internal and external label

Terminal Accom.: 14-8 AWG

• Terminal ID: In accordance with UL and international conventions

## Standards and Certifications

CE : CE Marked – Low Voltage Directive (LVD) 2014/35/EU

IEC: 60529NEMA: 250

• NOM: NOM-ANCE

cULus: Listed to UL 60947-4-1 (supersedes UL 508) and CSA-C22.2 no. 60947-4-1

## Warranty

Warranty: 3-Year Limited

## Product Features

Feature: Factory Installed Auxiliary Contact

\*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

#### SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:
JOB NUMBER:	

· Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):+1-800-824-3005

· Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386- 1797 ·

#### www.leviton.com.mx

· Visit our Website at: www.leviton.com

© 2021 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

· Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

#### **Documents / Resources**



<u>LEVITON MDS3-AC Power Switch Safety Disconnect Switch with Factory Installed Auxiliary Contact</u> [pdf] Instructions

MDS3-AC Power Switch Safety Disconnect Switch with Factory Installed Auxiliary Contact, MD S3-AC, Power Switch Safety Disconnect Switch with Factory Installed Auxiliary Contact, Power Switch Safety Disconnect Switch, Disconnect Switch, Switch

## References

- <u>O Leviton | Switches, Dimmers, Outlets & Lighting Controls</u>
- <u>S</u> Leviton
- O Leviton | Switches, Dimmers, Outlets & Lighting Controls
- Select Your Location

Manuals+