



LUTRON UVC-254A Uvc Light Meter User Manual

[Home](#) » [Lutron](#) » LUTRON UVC-254A Uvc Light Meter User Manual 



Contents

- [1 LUTRON UVC-254A Uvc Light Meter User Manual](#)
- [2 FEATURES](#)
- [3 GENERAL SPECIFICATIONS](#)
- [4 ELECTRICAL SPECIFICATIONS \(23± 5 °C\)](#)
- [5 Documents / Resources](#)
- [6 Related Posts](#)



Model : UVC-254A


ISO-9001, CE, IEC1010

FEATURES

- | |
|---|
| * Short wave 254 nm ultra-violet irradiance measurement. |
| * Professional, high quality UVC meter. |
| * Wide measurement range, 199.9 $\mu\text{W}/\text{cm}^2$, 1.999 mW/cm^2 and 19.99 mW/cm^2 . |
| * Microprocessor circuit assures maximum possible accuracy, provided special functions and features. |
| * Exclusive UVC sensor with correction filter. |
| * Super large LCD display, easy readout. |
| * Heavy duty & compact housing case. |
| * Records Maximum, Minimum with recall. |
| * Data hold. |
| * Auto power off saves battery life. |
| * Operates from 9V battery. |
| * RS232 PC serial interface. |
| * Zero adjustment by push button. |

GENERAL SPECIFICATIONS

Circuit	Custom one-chip microprocessor LSI circuit.		Size	Main instrument: 180 x 72 x 32 mm (7.1 x 2.8 x 1.3 inch). Sensor probe: 38 mm DIA. x 25 mm.
Display	13 mm (0.5") large LCD display. Dual function display.			
Spectral response range of sensor	Point	254 nm.		
	Band pass	200 -280 nm * Refer attached spectrum.	Accessories	Instruction manual..... 1 PC. UVC sensor probe..... 1 PC. Hard carrying case..... 1 PC.
Measurement & ranges	199.9 uW/cm^2 x 0.1 uW/cm^2 1.999 mW/cm^2 x 0.001 mW/cm^2 19.99 mW/cm^2 x 0.01 mW/cm^2		Optional accessories	* Data Acquisition software,SW-U801-WIN * Excel data Acquisition software,SW-E802 * RS232 cable.....UPCB-01 * USB cable.....USB-01
Linearity	± 1%.			
Sensor	The exclusive photo diode & UVC color correction filter.			
Memory Recall	Records Maximum & Minimum reading with recall.		Applications	No. UV-C has been used for over 100 years in various applications to kill germs on surfaces, in the air and in the water. UV-C has been proven to kill up to 99.9% of germs. Many hospitals use UV-C to sanitize. inks, adhesives and coatings.
Zero Adj.	By push button.			
Sample Time	Approx. 0.4 sec.			
Power off	Manual off by push button, or auto shut off after 10 minutes approximately.			

Over Range Indication	Indication of "- - - -"	UVC sensor spectrum 
Data output	RS 232/USB PC computer interface. * Connect the optional RS232 cable UPCB-02 will get the RS232 plug. * Connect the optional USB cable USB-01 will get the USB plug.	
Operating Temperature and Humidity	0 °C to 50 °C (32 °F to 122 °F). Max. 80% RH.	
Power Supply	DC 9V 006P, MN1604 (PP3) or equivalent. (Alkaline or Heavy duty type).	
Power Current	Approx. DC 5.3 mA.	
Weight	355 g/0.77 LB (included batteries)	

ELECTRICAL SPECIFICATIONS (23± 5 °C)

Range	Resolution	Accuracy
199.9 $\mu\text{W}/\text{cm}^2$	0.1 $\mu\text{W}/\text{cm}^2$	$\pm (3 \% \text{ FS } + 2 \text{ dgt})$ FS : full scale
1.999 mW/cm^2	0.001 mW/cm^2	
19.99 mW/cm^2	0.01 mW/cm^2	

* Appearance and specifications listed in this brochure are subject to change without notice.

Read More About This Manual & Download PDF:

	LUTRON UVC-254A Uvc Light Meter [pdf] User Manual UVC-254A Uvc Light Meter, UVC-254A, Uvc Light Meter, Light Meter
---	--