

CARSON®

MagniRead™

1.5x Magnifier Bar

MR-25

Congratulations on selecting your new MagniRead! In order to achieve optimum performance, please follow instructions for proper use and care.



PRODUCT SPECIFICATION

Magnification:	1.5x
Weight:	0.09 lbs
Dimensions:	0.9" x 0.6" x 6.3"

USING THE MAGNIFIER

Hold magnifier by handle. Start with magnifier flat on page and view text or numbers through yellow highlighted area.

For Best Results:

- Depending on your vision, you may need to raise magnifier slightly until text is clear.

CARE

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ info@carson.com



✉ uksupport@carson.com



✉ eusupport@carson.com

For warranty information, **visit www.carson.com/warranty**

www.carson.com

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000