

# CARSON®

## MagniRead™

### 1.5x Magnifier Bar

MR-25

Congratulations on selecting your new MagniRead! In order to achieve optimum performance, please follow instructions for proper use and care.



#### PRODUCT SPECIFICATION

Magnification:	1.5x
Weight:	0.09 lbs
Dimensions:	0.9" x 0.6" x 6.3"

#### USING THE MAGNIFIER

Hold magnifier by handle. Start with magnifier flat on page and view text or numbers through yellow highlighted area.

**For Best Results:**


- Depending on your vision, you may need to raise magnifier slightly until text is clear.

#### CARE

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

#### Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ [info@carson.com](mailto:info@carson.com)



✉ [uksupport@carson.com](mailto:uksupport@carson.com)



✉ [eusupport@carson.com](mailto:eusupport@carson.com)

For warranty information, **visit [www.carson.com/warranty](http://www.carson.com/warranty)**

**[www.carson.com](http://www.carson.com)**

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000