

DASH Centrifuges

High Performance STAT Processing



Model	Rotor Type	Interface	Preset Cycles Time / Speed / RCF	Max Speed RPM / RCF	Up to 13 x 75 mm or 5 mL			Dimensions (W x D x H)
DASH Apex 4 00-053-009-000	Fixed Angle	2-Button, 3-Setting	30 sec / 8500 RPM / 4440 xg 2 min / 8500 RPM / 4440 xg 3 min / 8500 RPM / 4440 xg	8500 / 4440	4			7 x 7 x 7 in 17.8 x 17.8 x 17.8 cm

Model	Rotor Type	Interface	Preset Cycles Time / Speed / RCF	Max Speed RPM / RCF	Up to 16 x 100 mm or 10 mL	Up to 16 x 125 mm or 15 mL	50 mL	Dimensions (W x D x H)
DASH Coag 00-676-009-001	Fixed Angle	2-Button, 3-Setting	2 min / 6600 RPM / 4400 xg 3 min / 6600 RPM / 4400 xg 5 min / 5200 RPM / 2700 xg	6600 / 4400	12	-	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm
DASH Flex 6 00-176-009-000	Horizontal	Digital, 10-Setting	3 min / 5300 RPM / 4000 xg 5 min / 5300 RPM / 4000 xg 10 min / 3800 RPM / 2000 xg	5400 / 4150	6	-	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm
DASH Flex 12 00-183-009-000	Horizontal	Digital, 10-Setting	3 min / 5200 RPM / 4000 xg 5 min / 5200 RPM / 4000 xg 7 min / 3600 RPM / 2000 xg	5200 / 4000	12	-	-	13 x 15 x 9 in 33 x 38.1 x 22.9 cm
DASH Flex 24 00-184-009-000	Horizontal	Digital, 10-Setting	5 min / 4300 RPM / 3150 xg 6 min / 4300 RPM / 3150 xg 7 min / 3500 RPM / 2100 xg	4500 / 3450	24	12	6	15 x 17 x 9 in 38.1 x 40.2 x 22.9 cm

(adapters available for a variety of tube sizes)

SERO 12 - Blood Banking Centrifuge

A drop-in replacement for the BD SeroFuge



Model	Rotor Type	Interface	Preset Cycle Time / Speed / RCF	Max Speed RPM / RCF	12 Place Rotor Up to 75mm	6 Place Rotor Up to 100 mm	Dimensions (W x D x H)
SERO 12 00-483-009-001	Fixed Angle	10-Setting, Digital	15 sec / 3600 RPM / 1040 xg	3600 / 1040	6 capped 12 uncapped	6	13 x 15 x 9 in 33 x 38.1 x 22.9 cm



All centrifuges are available
for a free 30-day evaluation.
Visit: druckerdiagnostics.com/evaluation-program

HORIZON Centrifuges

Quality Routine Chemistry



Model	Rotor Type	Interface	Preset Cycles Time / Speed / RCF	Max Speed RPM / RCF	Up to 16 x 100 mm or 10 mL	Up to 16 x 125 mm or 15 mL	50 mL	Dimensions (W x D x H)
HORIZON 6 Flex 00-376-009-000	Horizontal	Digital, 10-Setting	10 min / 3600 RPM / 1850 xg 15 min / 3300 RPM / 1500 xg 5 min / 1900 RPM / 500 xg	3800 / 2000	6	-	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm
HORIZON 6 Flex FA 00-376-009-001	Fixed Angle	Digital, 10-Setting	10 min / 3900 RPM / 1600-1850 xg 15 min / 3800 RPM / 1500 xg 5 min / 2200 RPM / 500-600 xg	3900 / 1850	6	6	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm
HORIZON 12 Flex 00-383-009-000	Horizontal	Digital, 10-Setting	10 min / 3500 RPM / 1800 xg 15 min / 3200 RPM / 1500 xg 5 min / 1800 RPM / 500 xg	3700 / 2000	12	-	-	13 x 15 x 9 in 33 x 38.1 x 22.9 cm
HORIZON 24 Flex 00-384-009-000	Horizontal	Digital, 10-Setting	10 min / 3300 RPM / 1800 xg 15 min / 3000 RPM / 1500 xg 5 min / 1700 RPM / 500 xg	3400 / 2000	24	12	6	15 x 17 x 9 in 38.1 x 40.2 x 22.9 cm

(adapters available for a variety of tube sizes)

600 Series Centrifuges

Compact Routine Chemistry



Model	Rotor Type	Interface	Preset Cycle Time / Speed / RCF	Max Speed RPM / RCF	Up to 16 x 100 mm or 10 mL	Up to 16 x 125 mm or 15 mL	50 mL	Dimensions (W x D x H)
614B 00-004-009-001	Fixed Angle	Dial, 1-Setting	1-30 min / 3250 RPM / 1200 xg	3350 / 1300	6	6	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm
642B 00-016-009-001	Horizontal	Dial, 1-Setting	1-30 min / 3380 RPM / 1600 xg	3380 / 1600	6	-	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm
642E 00-018-009-001	Horizontal	Dial, 1-Setting	10 min / 3380 RPM / 1600 xg	3380 / 1600	6	-	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm
642M 00-077-009-000	Horizontal	Dial, 1-Setting	10 min / 3400 RPM / 1600 xg	3400 / 1650	6	-	-	12 x 14 x 9 in 30.5 x 35.6 x 22.9 cm

(adapters available for a variety of tube sizes)

Questions? Contact Drucker Diagnostics Now.