


LED TABLE LAMP


User Manual



Thank you for purchasing this product.
Please read this instruction carefully to
understand its features and safety cautions.

FEATURES


- ◆ Use advanced LED technology, soft light without dazzle and ghosting, protecting your eyes.
- ◆ Long lifespan and low light attenuation.
- ◆ Touch control with three steps brightness and three modes for CCT.
- ◆ Memory function for the brightness and temperature
- ◆ Built-in rechargeable Lithium battery for emergency lighting
- ◆ Folding design, easy to packaging



SPECIFICATIONS

Item	LED TABLE LAMP
LED Power	4W
USB Cable Input	5V
CCT	3000±250K
	4500±250K
	5700±250K
Lifespan	35000h
CRI	≥80Ra
Center luminance(25cm)	≥600Lux
Charging Time	5~6h
Working Time	4hours(min) ≥8hours(max)
Capacity of Battery	2200mAH
Material	ABS+PS
Product size	200x52x260mm
N.W.	410g
Colors	White+Silver/White+ Champagne Gold/Black

PACKING LIST



Operation Cautions:

- 1.Please do not put the lamp on the high-temperature surfaces, and do not use it in flammable or humid environment, to avoid the breakdown, short circuit etc.
- 2.The adapter must be under the specialized range.
- 3.Please steady the base while adjusting the arm.
- 4.The lamp head can be adjusted freely under the adjustment range. But be cautious and never over adjustment to result in breakdown.

PARTS INDICATOR


Light Guide Panel
Heat emission hole

Blue light: The light is on
Red: The battery is charged
Green: The battery is fully charged

Compound Button/
Adjusting brightness and temperature

Adapter socket

OPERATION GUIDE



- Table Lamp mode with touch button. When touching this switch button, the lamp is on, and you can touch this button repeatedly to change the brightness and turn off the light with circulation by "minium light-medium light-maximal light-turn off"
- When you touch this button stays at any brightness step more than 2s, the light changes the temperature with circulation by "warm light-cold light-natural light"
- When you stays at any brightness and temperature step more than 20s,if you touch this button again, the lamp is off directly. When turning on the lamp next time, the brightness and temperature will be same as last time.

Maintenance

1. Please clear the lamp every two months to keep it smooth and bright.
2. Just use cleaning cloth and water to clean the dust.
3. For the filthy mark, please use cleaning cloth and soap suds.
4. Please do not clean the lamp by high-volatility and high-corrosive liquid which can make it discoloring or broken.




Power off before cleaning.
Please ask for the professional person for checking and repairing when it is broken.
If any abnormal cases, power off rapidly and contact dealer or manufacturer.

GUARANTEE

User Name: _____
Tel: _____
Address: _____
Purchasing Date: _____
Invoice No.: _____
Item No.: _____
Purchasing Store: _____
Serial No.: _____
Manufacture Date: _____

LED 便携式充电台灯

说明书



感谢您购买本产品。
请认真阅读本说明，了解其功能和安全注意事项。

性能特点

- 先进的发光技术，无炫目无频闪，灯光柔和护眼
- 超长寿命及极小光衰的发光导体
- 触控开关，可调三档亮度，三种色温
- 亮度色温记忆功能
- 内置可充电锂电池，可移动应急照明
- 折叠式设计，体积小易包装



三档调光



内置锂电池




三种色温




无辐射

产品结构



产品操作



- 复合式按键，用手指轻触按键，LED台灯随即点亮，重复触控此按键，即可操作“低亮—中亮—高亮—关机”的循环。
- 当在任意亮度下按住按键2秒后，即可操作“暖光—冷光—自然光”三种色温的循环。
- 用户在任何亮度色温档位停留时间超过20秒后，当再次短按按键，直接关机。下次开机时，自动开启上次关机时的亮度和色温。

参数规格

项目	LED便携式充电台灯
消耗功率	4W
USB输入	5V
色温	3000±250K
	4500±250K
	5700±250K
使用寿命	35000小时
显色指数	≥80Ra
中心照度(25cm)	≥600Lux
充电时间	5-6小时
工作时间	最亮4小时,最暗≥8小时
电池容量	2200毫安
材质	ABS+PS
尺寸	200×52×260mm
重量	410g
颜色	白+银/白+香槟金/黑色

包装清单



产品保养：

- 1、为保持产品表面的光洁明亮,请定期(建议两个月一次)进行清洁
- 2、清理普通灰尘时，只需用柔软的清洁布蘸清水擦拭
- 3、对无法用清水去除的污迹，请用清洁布沾肥皂水擦拭
- 4、请勿用高挥发性、高腐蚀性液体(如汽油、天那水等)擦拭灯具，以免变色或损坏



- 清理产品前请务必切断电源
- 产品发生故障时，请委托专业人员进行检查及维修
- 产品发生异常现象时，请迅速切断电源，并及时与经销商或厂家联系

保 修 回 执

电 话 _____
用户姓名 _____
地 址 _____
购买日期 _____
发票号码 _____
型号规格 _____
购货商场 _____
出厂编号 _____
出厂日期 _____