

Fiber Coupled 90° Optical Hybrid



DATASHEET

[Return to the Webpage](#)



Features

- Passive
- Compact Size
- Polarization Diversified Version Also Available

Applications

- Optical Coherent Detection
- QPSK Demodulation

The FCOH is a passive, micro-optics-based 90° optical hybrid designed for coherent optical signal demodulation, including BPSK and QPSK formats. It functions by mixing the incoming signal (S) with a local oscillator reference signal (L), generating four optical outputs corresponding to the vector sums and differences of the two inputs: $S+L$, $S-L$, $S+jL$, and $S-jL$. These outputs represent four quadrature states in the complex optical field space. The signals are then directed to two pairs of balanced photodetectors, enabling differential detection of the in-phase (I) and quadrature (Q) components. This configuration allows extraction of both amplitude and relative phase information through digital signal processing. In a coherent receiver system, preserving the optical phase enables advanced functionalities such as dispersion compensation and phase noise mitigation in the electrical domain, improving overall system performance and enabling cost-effective compensation of optical transmission impairments. A block diagram illustrating the integration of the 90° Optical Hybrid in a coherent receiver is shown below.

Specifications

Parameter	Min	Typical	Max	Unit
Wavelength Range (C- or L-Band)	1527		1567	nm
Phase Difference ^[1] (between M ₁ , M ₂ and M ₃ , M ₄)		90 ± 5		deg
Insertion Loss ^[1] (without connector)	S→Mi	< 8.5		dB
	L→Mi	< 8.5		
Insertion Loss Difference ^[1]	between S→M ₁ and S→M ₂	< 1.2		dB
	between S→M ₃ and S→M ₄	< 1.2		
	between L→M ₁ and L→M ₂	< 1.2		
	between L→M ₃ and L→M ₄	< 1.2		
Optical Return Loss		> 27		dB
Optical Path Difference (skew, between M ₁ and M ₂ and between M ₃ and M ₄)		< 1		ps
Optical Path Difference (skew, between any other two outputs)		< 2 in fiber length		mm
Operating Temperature	15		35	°C
Storage Temperature	-40		85	°C
Optical Power Handling (CW)		300	500	mW
Fiber Type	SMF-28 with 900 μm loose tube			
Connector Type	TBD			

Notes:

- [1]. Over the stated spectral and operating temperature ranges and all polarization states.
- [2]. Subject to change, not including collimator sleeves extending from the two adjacent sides by 21 mm.

Note: The specifications provided are for general applications with a cost-effective approach. If you need to narrow or expand the tolerance, coverage, limit, or qualifications, please [click this link](#):




Legal notices: All product information is believed to be accurate and is subject to change without notice. Information contained herein shall legally bind Agiltron only if it is specifically incorporated into the terms and conditions of a sales agreement. Some specific combinations of options may not be available. The user assumes all risks and liability whatsoever in connection with the use of a product or its application.

Rev 07/11/25

Fiber Coupled 90° Optical Hybrid

DATASHEET

Function Diagram



Electronic Control Requirements

Fiber Coupled 90° Optical Hybrid



 DATASHEET |

Mechanical Dimension

*Product dimensions may change without notice. This is sometimes required for non-standard specifications.

Recommendation Control Circuit

Fiber Coupled 90° Optical Hybrid



DATASHEET

Ordering Information

	11	B	1	1	1	3	☐	☐
Prefix	Type	Wavelength		Version		Fiber Cover	Fiber Length	Connector
FCOH-	Regular = 11 Special = 00	1260~1620 = B Special = 0		Standard = 1 Special = 0		900 um tube = 3 Special = 0	0.25m = 1 0.5m = 2 Special = 0	None = 1 FC/PC = 2 FC/APC = 3 SC/PC = 4 SC/APC = 5 LC/PC = 7 Duplex LC/PC = 8 Special = 0

☐ PM1550 fiber works well for 1310nm

Fiber Core Alignment

Note that the minimum attenuation for these devices depends on excellent core-to-core alignment when the connectors are mated. This is crucial for shorter wavelengths with smaller fiber core diameters that can increase the loss of many decibels above the specification if they are not perfectly aligned. Different vendors' connectors may not mate well with each other, especially for angled APC.

Fiber Cleanliness

Fibers with smaller core diameters (<5 µm) must be kept extremely clean, contamination at fiber-fiber interfaces, combined with the high optical power density, can lead to significant optical damage. This type of damage usually requires re-polishing or replacement of the connector.

Maximum Optical Input Power

Due to their small fiber core diameters for short wavelength and high photon energies, the damage thresholds for device is substantially reduced than the common 1550nm fiber. To avoid damage to the exposed fiber end faces and internal components, the optical input power should never exceed 20 mW for wavelengths shorter 650nm. We produce a special version to increase the handling by expanding the core side at the fiber ends.