USER GUIDE





FULL HD 1080P WEBCAM WITH RING LIGHT

KAWCMHDLKTA

INSTALLATION

This webcam is plug-n-play, requiring no additional drivers or software to install. Simply insert into a USB 2.0 compatible port and your computer will recognise it as a camera option. To set as the default camera across all apps/programs, you may need to adjust your settings.

Windows 10: Settings > Privacy > Camera

macOS: Open PhotoBooth to change the computer's default camera from iSight to your Kogan USB Webcam.

Operating the camera:

Turn the round knob in the middle to adjust the focal lens.

To adjust the brightness, use the lighting dial in the USB cable.







SPECIFICATIONS

Dynamic Pixels 200W Pixels

Speed Rate 30 FPS

Signal-to-Noise ratio 85db

Recommended Resolution 1960 x 1080 Output

Format USB 2.0 uncompressed YUY2 or MJPG

Interface USB 2.0 compatible with USB 1.1

Max: 150 lux Lumen per square metre

Min: 2 lux

70cm-90cm **Imaging Range**

Scintillation Control 50Hz or 60Hz

Static Image Capture Format BMP/JPEG/PNG

Sensor CMOS 1/4 Colour Chip

Lens 2P2G

LED lamp beads 4

NOTES

NOTES



Need more information?

We hope that this user guide has given you the assistance needed for a simple set-up. For the most up-to-date guide for your product, as well as any additional assistance you may require, head online to **help.kogan.com**

