SmallRig



mini Cold Shoe to 14-20 Screw Adapter Support



SmallRig Mini Cold Shoe to 1/4" Screw Adapter 3577 is mainly used for expansion of small fill light, allowing 138° pan/tile adjustment, and stop at any position due to its damping structure, realizing precise lighting. It can be connected to the hot shoe at the top of the camera via the cold shoe port, or installed at the cold shoe port of cage or grip. The fill light can be connected via a 1/4"-20 screw hole. Anti--scratch pads are provided at the top to increase the locking friction and protect the device from scratch. Weighing only 20g, the adapter is compact and portable.

Safety Guidelines

1 Environment

2. Load Capacity

Do not use the product underwater, in extreme temperatures (e.g., freezing or direct heat), corrosive environments, or excessive dust. Dry metal parts immediately after liquid contact to prevent corrosion.

Do not exceed the maximum weight capacity indicated on the product.

Overloading risks structural failure, deformation, or accidental drops.

3. Cleaning & Maintenance

Clean surfaces with a dry, soft cloth. Avoid chemicals like alcohol or solvents. Ensure dry and ventilated conditions for long-term storage.

Structural Integrity Do not modify the product (e.g., drilling, cutting)—this compromises structural

integrity and increases drop risks. 5 Malfunctions

Stop use immediately if you notice deformation, unusual noises, or loose components, and contact support.

In the Box

Mini Cold Shoe to 1/4"-20 Adapter

Product Details













Wide Compatibly





ROB Weller Light El-1098



MOR VIOLATION



do 1941



Universal Video Kit 85-3615

Adjustment

For the expansion of small fill light, allowing 138° pan and tile adjustment and realizing precise lighting.





Package Includes

more Cold Shore to U.S'-20 Adapter + 1



Product Parameters

Street, .

12 6 + 24 + 25 hours

.

55 + 56 + 62mm

Abstract Ship,

Billia Def

22 x 50

9577

Manufacturer Email: support@smallrig.com Manufacturer: Shenzhen Legi Innovation Co. Ltd.

Add: Rooms 101, 701, 901, Building 4, Gonglianfuii Innovation Park, No. 58, Ping'an Road. Dafu Community, Guanlan Street, Longhua District, Shenzhen, Guangdong, China.

Consignor Shenzhen LC Co. Ltd.

Add: Room 201, Building 4, Gonglianfuji Innovation Park, No. 58, Ping'an Road, Dafu Community, Guanlan Street, Longhua District, Shenzhen, Guangdong, China.

























Made in China

Séparez les éléments avant de trier