



Contents [[hide](#)]

- [1 ProDevice V.DSS.2025.1 Drawer Storage System](#)
- [2 Product Usage Instructions](#)
- [3 INTRODUCTION](#)
- [4 SYMBOLS](#)
- [5 FEATURES](#)
- [6 PACKAGING REMOVAL](#)
- [7 OVERVIEW](#)
- [8 INSTRUCTION VIDEO](#)
- [9 STORAGE OF MEDIA](#)
- [10 MAINTENANCE](#)
- [11 CUSTOMER SERVICE](#)
- [12 FAQ](#)
- [13 Documents / Resources](#)
 - [13.1 References](#)



ProDevice V.DSS.2025.1 Drawer Storage System



Specifications

- **Product:** ProDevice DSS Data Cabinet
- **Model:** V.DSS.2025.1.EN
- **Manufacturer:** DISKUS Polska Sp. z o. o.
- **Material:** High-quality steel with powder coating finish
- **Dimensions:** External – 155 x 950 x 523 mm (6.1 in x 37.4 in x 20.6 in), Internal – 142 x 905 x 473 mm (5.6 in x 35.6 in x 18.6 in)
- **Capacity:** DSS 500 – 1 small drawer: approx. 600 tapes, DSS 600 – 2 bigger drawers: approx. 792 tapes

Product Usage Instructions

Packaging Removal

- Remove all packaging materials and place the cabinet on a firm surface at the designated installation site. Secure the cabinet to prevent movement.

Overview

- The cabinet consists of drawers with adjustable separating barriers for different types

of media. Ensure even distribution of components in each drawer, and do not exceed a load of 50 kg per drawer.

Instruction Video

- Scan the QR code provided in the manual to watch a video demonstrating the correct usage of the cabinet.

Storage of Media

- Load storage media starting from the bottom drawer and distribute components evenly. Do not exceed the maximum load capacity and never sit on top of the cabinet.

Maintenance

- Clean the cabinet with a soft cloth and water only, avoiding entry of water into the device. Do not use harsh cleaning agents or perform mechanical maintenance yourself; contact the manufacturer's authorised service for any issues.

INTRODUCTION

- Thank you for purchasing the ProDevice DSS – Drawer Storage System – an excellent solution for secure storage and archiving of data media (like magnetic tapes, disk drives, floppy disks, and more).
- This product is made of high-quality steel and finished with powder coating.
- This user manual is integral to the device. Read and understand the manual before operating the cabinet. Keep the manual for future reference.
- The company Diskus Polska sp. z o. o., as the manufacturer is not responsible for the partial or total failure to comply with this manual.
- Strictly follow the operating guidance specified in the user manual. Any deviation from it is against the intended use of the cabinet. The manufacturer will not be liable for any damage caused by non-intended use of the device.
- Never attempt to modify the cabinet. The manufacturer will not be liable for the performance or operating safety if the device is modified.
- The manufacturer reserves the right to introduce changes to the design of devices,

deemed necessary by the manufacturer, to improve them.

SYMBOLS



Refer to Instruction manual.



Close the drawers with caution.



No sitting.

FEATURES

- **Dimensions:** 1071 mm x 1005 mm x 590 mm (42.2 in x 39.6 in x 23.2 in).
- **Weight:** DSS500 171 kg (377 lb) / DSS600 176 kg (388 lb).
- Drawers lined with a damping mat, which additionally protects the carriers, also minimise the possibility of media movements.
- Separation barriers.
- A locking mechanism that prevents pulling out several drawers at the same time.
- Ultra Track lock (two keys included).
- Self-levelling feet.

PACKAGING REMOVAL


- The DSS cabinet is delivered to the buyer in a dedicated box on a pallet. The device's weight requires at least two people to remove it from the pallet. Carefully remove all packaging materials and verify that the contents are complete as listed in the product features above. Having removed the packaging materials, immediately inspect the cabinet for any evidence of damage in transport. If the device or any of its dedicated accessories are damaged, report this to the shipment forwarder and the manufacturer.
- With all packaging materials removed, place the cabinet on a firm surface at the designated, sheltered installation site. Secure the device in position to prevent movement.

OVERVIEW


	DSS 500	DSS 600
Number of drawers with dimensions: ext. 115 × 950 × 523 mm (4.5 in x 37.4 in x 20.6 in) int. 102 × 905 × 473 mm (4.0 in x 35.6 in x 18.6 in)	1	5
Number of drawers with dimensions: ext. 155 x 950 x 523 mm (6.1 in x 37.4 in x 20.6 in) int. 142 x 905 x 473 mm (5.6 in x 35.6 in x 18.6 in)	5	2
Capacity (LTO tapes without boxes in a small drawer and LTO tapes with boxes in a bigger drawer)	approx. 600 tapes	approx. 792 tapes

- Drawers for data carriers are equipped with separating barriers, which can be freely configured, depending on the type of media stored in a given drawer.

HARD DRIVE DISKS



MAGNETIC TAPES



INSTRUCTION VIDEO

- Scan the QR code to watch an official video presenting the correct usage of the ProDevice DSS cabinet.



- The video is an inseparable part of this manual Instruction.

STORAGE OF MEDIA

- Begin loading storage media from the lowest level (bottom drawer) of the ProDevice DSS. Each ProDevice DSS drawer must be loaded with evenly distributed components.
- Do not exceed a maximum load of 50 kg per drawer.



- **DANGER!** Never attempt to sit on top of the DSS media cabinet!

MAINTENANCE

- Only clean the machine with a soft cloth and water. Do not allow water to enter the device. Do not use scouring agents, cleaning fluids, petroleum, or thinners.
- Mechanical maintenance may only be performed by the manufacturer's authorised service.
- In the event of a failure or interruption in operation due to damage to the device or any of its components, contact the authorised service of the manufacturer.

CUSTOMER SERVICE

- INTERNATIONAL HOTLINE: +48122919101

CONTACT

- ProDevice Limited Liability Company
- Kościuszki Street 1, 32-020 Wieliczka, Poland
- tel. +48 122 919 101
- e-mail: info@pro-device.com
- service: support@pro-device.com
- If you have an improvement idea or suggestion, write to info@pro-device.com
- info@pro-device.com
- www.pro-device.com

MANUFACTURER'S ADDRESS DETAILS

- DISKUS Polska Limited Liability Company, ul. Kościuszki 1, 32-020 Wieliczka, Poland
- service: support@pro-device.com
- www.pro-device.com

FAQ


Can I modify the cabinet?

No, any modification to the cabinet is not recommended and may affect its performance and safety.

How should I clean the cabinet?

Use a soft cloth with water for cleaning; avoid using scouring agents, cleaning fluids, petroleum, or thinners.

Documents / Resources

	ProDevice V.DSS.2025.1 Drawer Storage System [pdf] Installation Guide V.DSS.2025.1 Drawer Storage System, V.DSS.2025.1, Drawer Storage S ystem, Storage System, System
--	--

References

- [User Manual](#)

ProDevice
Drawer Storage System, ProDevice, Storage System, System, V.DSS.2025.1, V.DSS.2025.1 Drawer Storage System

Leave a comment

Your email address will not be published. Required fields are marked *

Comment *

Name

Email

Website

☐ Save my name, email, and website in this browser for the next time I comment.

Post Comment

Search:

e.g. whirlpool wrf535swhz

Search

[Manuals+](#) | [Upload](#) | [Deep Search](#) | [Privacy Policy](#) | [@manuals.plus](#) | [YouTube](#)

This website is an independent publication and is neither affiliated with nor endorsed by any of the trademark owners. The "Bluetooth®" word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. The "Wi-Fi®" word mark and logos are registered trademarks owned by the Wi-Fi Alliance. Any use of these marks on this website does not imply any affiliation with or endorsement.