

YVV Turner Cup Rotating Display Stand



YVV Turner Cup Rotating Display Stand User Guide

[Home](#) » [YVV](#) » YVV Turner Cup Rotating Display Stand User Guide 

Contents

- [1 YVV Turner Cup Rotating Display Stand](#)
- [2 Product Feature](#)
- [3 Specifications](#)
- [4 After-sales maintenance](#)
- [5 Get 12 months after-sale warranty](#)
- [6 Documents / Resources](#)
 - [6.1 References](#)




YVV Turner Cup Rotating Display Stand



Thank you for using our product. For your safety, please read this user manual carefully before installing it.

Product Feature

360-degree rotating display product or product photography shots or video.




Standard configuration	
Turntable	1 piece
USB Cable	1 piece



Specifications

Item No	Material	Color	Speed	Max load capacity	Voltage
ND-120	Plastic	White	15 s/lap	2KG	DC 5V/0.5A
ND-160	Plastic	White	17 s/lap	3KG	DC 5V/0.5A



Notes

- Do not overload on the turntable.
- The ambient temperature must always be between 5°C to + 45°C use under indoor dry conditions.
- Never touch the device with wet hands, as it could lead to mortal electrical shock or injury.
- Any unauthorized modifications to the device are forbidden due to safety considerations.
- Normal noise value within 55 decibels during product operation.
- USB data cable and battery (not included) cannot be used at the same time to charge the battery!

After-sales maintenance

- Disconnect from mains before starting maintenance operation.
- We recommend a frequent cleaning of the device. Please use a soft lint-free dry cloth. Never use alcohol or solvents.


- Maintenance should be carried out by qualified professionals only.

Get 12 months after-sale warranty



Edit order number + name to
YVVservice@outlook.com

Documents / Resources



Electric Turntable Instructions

Thank you for using our product. For your own safety, please read this user manual carefully before installing it.

Product Feature

360 Degree rotating display product or for product photography shots or video.

Standard configuration

Turntable	1 piece
USB Cable	1 piece

Specifications

Item No.	Material	Color	Brand	Max load capacity	Weight
ND-120	Plastic	White	YVV	200g	120g
ND-160	Plastic	White	YVV	250g	160g

Dimensions

120MM (Diameter)
45MM (Height)

ND-120

160MM (Diameter)
50MM (Height)

Indicator Light

1. Turn left: Clockwise rotating
2. Turn right: Counter-clockwise rotating
3. Middle position: Power off

Notes


Do not overload on the turntable.
(The ambient temperature must always be between 5°C to 45°C use under indoor dry condition.
Avoid touch the device with wet hands, we must avoid to avoid electrical shock or injury.
Also, avoid contact with dust or dirt on the device to avoid damage due to safety consideration.
Normal value within 15 degrees during product operation.
① USB cable and battery (not included) cannot be used at the same time to charge the battery.

After-sales maintenance

Disconnect from mains before starting maintenance operation.
We recommend a frequent cleaning of the device.
Please use a soft lint-free dry cloth. Never use alcohol or abrasive.
Maintenance should be carried out by qualified professional only.

Get 12 months after-sale warranty

Edit order number + name to
YVVservice@outlook.com



[YVV Turner Cup Rotating Display Stand \[pdf\] User Guide](#)

Turner Cup Rotating Display Stand, Turner, Cup Rotating Display Stand, Rotating Display Stand , Display Stand, Stand

References

- [User Manual](#)

